

EIZO Unveils FlexScan® S2242W and FlexScan® S2232W LCD Monitors for Financial Trading and Corporate Offices

Hakusan, Japan, February 3, 2009 - Eizo Nanao Corporation (TSE: 6737) today introduced two

22" widescreen LCD monitors, the FlexScan S2242W and FlexScan S2232W.



The FlexScan S2242W offers a native resolution of 1920 × 1200, the same resolution offered by a 24.1" wide format monitor. The monitor's 0.247 mm pixel pitch and display of 103 pixels per inch reveals 24-inches of information on a 22" screen.

Occupying 10% less desk space than a typical 24.1" monitor, the FlexScan S2242W is ideal for financial trading or corporate offices where a 24.1" monitor is desired, but cannot be installed due to space constraints.

Also unveiled, the FlexScan S2232W has a standard native resolution of 1680×1050 and the same performance as the FlexScan S2242W. Both models employ vertical aligned (VA) panel technology, offer wide 178° viewing angles, brightness of 350 cd/m², 1200:1 contrast ratio, and a 16:10 aspect ratio.

For reduced operating costs, increased user comfort and minimized impact on the environment, these monitors incorporate a wide array of "EcoView" Features. One such feature is Auto EcoView for automatic setting of brightness to the ideal level. With Auto EcoView turned on, the FlexScan S2242W and FlexScan S2232W operate with improved visual ergonomics and greater energy efficiency than with it turned off, typically consuming 33 watts and 42 watts, respectively.¹

These monitors have a feature called EcoView Index to encourage environmental consciousness while working. EcoView Index displays an on-screen index that correlates the level of power savings with the monitor's brightness setting. EcoView features also include a selection of ergonomic stands for proper viewing posture, and EIZO's EyeCare software utility which prompts workers to take scheduled breaks to rest their eyes.

Designed to reduce the electricity consumption of up to 2000 monitors, EIZO's EcoView NET power management software features centralized control over network monitor's power settings. Decreasing the power consumption of network monitors can lead to significant long-term energy savings while also reducing an institution's carbon footprint. Compatible with Microsoft® XP, Vista®, Server 2003 and 2008, EcoView NET's software's settings include turning the monitors' power and Auto EcoView on or off. ²

The FlexScan S2242W and FlexScan S2232W carry the 2009 version of EIZO's in-house environmental label – EIZO Eco Products (EEP). Since its inception in 2002, EEP has set strict internal requirements for manufacturing and packaging. As EIZO Eco Products 2009 labeled products, the monitors do not consume any power when turned off, use less than 1.5 watts in power save mode, and have their eco profiles available on eizo.com.



Both models feature a wide color gamut that reproduces 95% of Adobe RGB. For digital camera photo enthusiasts, these monitors are compatible with the optional accessory EIZO EasyPIX, a color matching tool that includes EasyPIX software and EIZO's EX1 color sensor. With EasyPIX, users can measure and save the monitor's settings to make color profiles for simple monitor and photo print color matching.

Additional Features

- One DVI-D (digital) and one D-Sub (analog) input.
- DVI input level adjustment to compensate for image quality degradation that may occur when connecting a monitor with a signal switch box or via a long cable.
- Advanced factory adjustment of gamma minimizes discrepancies of gamma characteristics and produces more uniform color between monitors.
- Dual 0.5 watt internal speakers. The optional i-Sound L3 speaker unit (0.9 watts) is also available if greater audio capability is needed.
- Optional QM1 quick mount attachment to allow the monitors to be quickly and easily mounted and dismounted.
- Five-year manufacturer's limited warranty.³

Availability

The FlexScan S2242W and FlexScan S2232W are now shipping. Date of availability varies by country and territory, so please contact your nearest EIZO subsidiary or distributor for details.

About EIZO

Eizo Nanao Corporation is a leading global manufacturer of high-end visual display products with a wide range of LCD monitors. The image quality, long-term reliability, and innovative features of EIZO monitors make them the products of choice in many financial trading rooms, hospitals, back offices, and design studios throughout the world. EIZO is based in Japan and represented in over sixty countries by a network of subsidiaries and exclusive distributors.

For more information, please contact: Eizo Nanao Corporation

153 Shimokashiwano

Hakusan, Ishikawa 924-8566

Japan

Phone: +81 76 277-6792 Fax: +81 76 277-6793

http://www.eizo.com/

###

All product names are trademarks or registered trademarks of their respective companies. EcoView NET and EasyPIX are trademarks, EIZO and FlexScan are registered trademarks of Eizo Nanao Corporation.

¹When set at default brightness of 100% and without Auto EcoView turned on, the FlexScan S2242W consumes 69 watts and the FlexScan S2232W consumes 66 watts of electricity.

² EIZO EcoView NET is compatible with FlexScan EV2411W, S2402W, S2202W, S2232W, S2242W.

³ The usage time is limited to 30,000 hours and the warranty period of the LCD panel is limited to three years from the date of purchase.