



EIZO Introduces FlexScan® M1900 LCD Monitor for Office Computing

Hakusan, Japan, December 13, 2005 – Eizo Nanao Corporation (“EIZO”) today unveiled the FlexScan M1900 19-inch LCD monitor for corporate and administrative offices. Equipped with built-in speakers, five imaging modes, and an industry-leading five-year warranty, the FlexScan M1900 is a versatile and reliable product at a low total cost of ownership.



From text and spreadsheet applications to web browsing, the FlexScan M1900 is ideal for a wide range of office applications.

It has a 1280 × 1024 native resolution, horizontal and vertical viewing angles of 170° and 155° respectively (at a contrast ratio of 5:1), brightness of 250 cd/m², and contrast ratio of 700:1. DVI-D and D-Sub input terminals are included to accept digital and analog signals. For multimedia applications, dual one-watt speakers are built into the cabinet. Volume and mute controls are available in the OSD menu, and a headphone jack is included.

For optimal viewing, the stand offers a 50 mm height adjustment range and the screen can be tilted 35 degrees. The power supply unit is built-in, and the monitor can be removed from the stand for mounting. The control buttons are arranged in a cross pattern on the three-tier front panel for simple and intuitive use.

The FlexScan M1900 comes with several image and color control features. The Fine Contrast function offers modes for office applications (Text mode), video clips (Movie) mode, graphics (Picture mode), web browsing (sRGB mode) and individual user settings (Customer mode). Toggling between modes is done by pressing a button on the front panel. An internal 10-bit look-up table offers a palette of over 1 billion colors from which the most appropriate 16.7 million (8-bits) are displayed, ensuring accurate reproduction of subtle color variations. Manual adjustment of gamma values from 1.4 to 3.0 in steps of 0.2 and color temperature from 4,000 to 10,000 K in steps of 500 K are available in the on-screen display menu, as are hue, gain, and saturation.

The FlexScan M1900 complies with some of the strictest standards for office equipment including TCO’03 (gray cabinet only; black cabinet is TCO’99 compliant) and TÜV Rheinland/Ergonomics. It also carries the EIZO Eco Products 2004 in-house label signifying that it meets several strict internal requirements such as the use of lead-free solder and chrome-free steel plates.

EIZO stands behind the workmanship of the FlexScan M1900 with an industry-leading five year warranty*. This warranty is valid in every country and territory where EIZO authorized distributors are located.

EIZO offers a wide variety of accessories for enhancing convenience and flexibility including a panel protector and mounting arms and stands. For more information, please see www.eizo.com/products/accessories/.



Availability

The FlexScan M1900 is now shipping and will go on sale worldwide in late January 2006. The cabinet will be available in both gray and black.

About EIZO

Eizo Nanao Corporation is a leading global manufacturer of high-end visual display products with a wide range of LCD monitors and Windows-Based Terminals. The image quality, long-term reliability, and innovative features of EIZO monitors make them the products of choice in many financial trading rooms, hospitals, back offices, and design studios throughout the world. EIZO is based in Japan and represented in over thirty countries by a network of exclusive distributors.

For more information, please contact:

Eizo Nanao Corporation
153 Shimokashiwano
Hakusan, Ishikawa 924-8566
Japan
Phone: +81 76 277-6792
Fax: +81 76 277-6793
<http://www.eizo.com/>

#

* The usage time is limited to 30,000 hours or less, and the warranty period of the LCD panel and backlight is limited to three years from the date of purchase.

All product names are trademarks or registered trademarks of their respective companies. EIZO, FlexScan, and MultiEdge are registered trademarks of Eizo Nanao Corporation.