



EIZO Unveils New High-End 19" CRT Monitor

FlexScan® T765's ultra-sharp images, high resolution range, and user oriented features ideal for graphics intensive and multimedia applications



Matto, Japan, July 19, 2001 – Eizo Nanao Corporation today introduced the FlexScan T765, a 19-inch (17.8" viewable) flat-faced CRT monitor for discriminating users seeking superior quality and performance. With high resolution capabilities, a USB hub with one upstream and four downstream ports, and an enhanced Fine Contrast function for application customization, the FlexScan T765 is well-suited for CAD/CAM, DTP, DIP, or multimedia applications. It also features a new CRT with an extremely high maximum brightness level of 230 cd/m².

“The FlexScan T765 is designed not only bring out the finest of details, but also to provide the user with convenience and time saving features such as a USB hub and a front-button operated Fine Contrast function,” said Kunihiro Arata, General Manager of Eizo Nanao Corporation’s Overseas Sales & Marketing Division. “The combination of leading features, specifications, and outstanding image quality only available from EIZO should make this the favorite in the 19" class among graphics professionals who will settle for nothing less than the best.”

The FlexScan T765 delivers sharp, crisp images from corner to corner with its flat-faced aperture grill CRT and a trio pitch of 0.24 mm in the center and 0.25 mm at the edges. The recommended resolution is 1280 × 1024 at a maximum refresh rate of 107 Hz. For extremely detailed text and graphic display, the FlexScan T765 has a maximum resolution capability of 1600 × 1200 at a flicker-free refresh rate of 92 Hz. It includes dual inputs (D-Sub mini 15-pin & BNC × 5) with a user selectable input priority function that ensures the most important data is always displayed on screen. Free toggling between the two inputs is possible by pressing a button on the front bezel.

Application Customization with Fine Contrast

The FlexScan T765 comes with Fine Contrast, an EIZO original feature that allows users to quickly optimize the display settings for any application. Fine Contrast includes Text, Browser, Picture, Graphic, and Movie modes, each with unique brightness, contrast, and color temperature settings. Front-button operation provides smooth navigation among the modes, while further adjustments to image parameters can be made with the OSD menu. The Movie mode maximizes the 230 cd/m² brightness level of the CRT for eye-catching playback of streaming video and DVDs.

An sRGB mode¹ is also included with Fine Contrast for color matching with software and other peripheral devices including scanners, printers, and digital cameras that also support the sRGB color space.



ScreenManager® Pro for USB²

Bundled with the FlexScan T765, this software program offers control over screen parameters using just the mouse or keyboard when the host PC is connected through the USB port. It also allows the user to adjust the brightness and contrast of a foreground window independently of background windows. Especially suitable for streaming video and DVD playback, the user can darken surrounding windows to more comfortably view the media player software window.

Compliance with Leading Energy and Ergonomic Standards

EIZO's own PowerManager™ and an off timer cut power consumption to less than three watts when the monitor is not in active use for significant energy savings as well as EPA ENERGY STAR® Program and Energy 2000 compliance.

With EIZO's focus on ergonomics, safety, and the environment, the FlexScan T765 meets the requirements for TÜV ECO Circle 2000 and TCO'99, the most stringent of Europe's certification standards.

i-Sound™ Sound Unit

For audio enhancement of multimedia applications, EIZO offers the i-Sound. This sound unit slides onto the front bezel of the monitor and is equipped with two speakers, two stereo mini-jack cables, and a microphone, all powered directly from the monitor. Several external jacks are provided for headphones, a headset, CD or tape players. The unit is sold separately.

About EIZO

Eizo Nanao Corporation, the specialist in the development and production of state-of-the-art display systems, is based in Japan and represented in over thirty countries by a network of exclusive distributors.

For more information, please contact:

Eizo Nanao Corporation
153 Shimokashiwano
Matto, Ishikawa 924-8566
Japan
Phone: +81 76 277-6792
Fax: +81 76 277-6793
<http://www.eizo.com/>

¹The sRGB mode is only accessible through the OSD menu.

²Compatible with Microsoft® Windows® 98 SE, Windows Me, and Windows 2000 operating systems only.

All product names are trademarks or registered trademarks of their respective companies. i-Sound and PowerManager are trademarks, and FlexScan and EIZO are registered trademarks of Eizo Nanao Corporation.