

AXIS (VAPIX)

Camera	Camera Firmware	Version 4.3xxx	Version 4.20xx	Version 4.10xx	Version 4.00xx	Version 3.00xx	Version 2.00xx	Version 1.00xx
F41	6.30.1	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1004-W	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1014	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1025	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1034-W	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1054	5.50.3.7	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1103	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1104	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1113	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1113-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1114	5.50.3	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1114-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1124	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1124-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1125	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1125-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1144-L	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1145	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M1145-L	5.55.3.1	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M3004-V	5.40.5.4	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M3007-P	5.75.1.1	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M3037-PVE	5.75.1.2	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M3045-V	6.15.4	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M3058-PLVE	7.45.1.2	Yes *2	N/A	N/A	N/A	N/A	N/A	N/A
P3904-R	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3905-R	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3905-RE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3915-R	5.80.1.2	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M5013	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M5013-V	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M5014	5.50.3	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M5014-V	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M5525-E	7.25.1	Yes *3	N/A	N/A	N/A	N/A	N/A	N/A
M7011	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M7014	5.50.4.1	Yes	Yes	Yes	N/A	N/A	N/A	N/A
M7016	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1346	5.40.9.6	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1346-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1353	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1353-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1354	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1354-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1357	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1357-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1365	5.75.3.2	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1365-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1365 Mk II	5.85.4	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1405-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1405-LE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1425-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1425-LE	5.80.1.2	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1427-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1427-LE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1428-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1435-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P1435-LE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3214-V	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3214-VE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3215-V	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3215-VE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3224-LV	6.30.1	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3224-LVE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3225-LV	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P3225-LVE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P5624-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
P5635-E	6.20.1.3	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q1604	5.90.1.1	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q1604-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q1614	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q1614-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q1615	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q1615-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q1635	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q1635-E	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q3505	6.30.1	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q3505-V	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q3505-VE	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A

AXIS (VAPIX)

Q6114-E	6.20.1.4	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q6115-E	6.20.1.3	Yes	Yes	Yes	N/A	N/A	N/A	N/A
Q7404	5.50.4.4	Yes	Yes *1	Yes *1	N/A	N/A	N/A	N/A
V5914	-	Yes	Yes	Yes	N/A	N/A	N/A	N/A
V5915	5.75.1.1	Yes	Yes	Yes	N/A	N/A	N/A	N/A

\*1

- IP Decoding Monitor supports only D1(720x480/720x576) in channel 2 to 4.

\*2

- Setting stream profile of video setting to none is required.

\*3

- Moving the preset position is not available.
- The PTZ operations are not supported.